

Elitech V900 Intelligent HVAC Vacuum Pump Automotive 9 CFM 2 Stage Touch Screen App



Elitech 2-STAGE INTELLIGENT VACUUM PUMP	
Model:	V-900
Free Air Displacement:	9 CFM
Ultimate Vacuum:	15 microns
Motor Size:	1 HP
Voltage:	110V ~ 60Hz
S/N:	



Authorized Distributor
APL ASIA CO., LTD.
11/129-132 Moo.5 Lamlukka Rd.,T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.
TEL. 0-2995-4461-3, FAX. 0-2995-4464
www.apl-asia.com
EMAIL : sales@apl-asia.com
LINE@ : @APL-ASIA

Elitech[®]
Innovation Preceding All

2
STAGE

9CFM
RATE

1HP
POWER

Dry Rotary Vane
Pump Type

110V/60Hz
Voltage

15 Microns
Ultimate Vacuum



Leakage
Level



Vacuum
Graph



Intelligent Control
Motor & Solenoid Valve



Estimate
Complete Time



4" Touch
Screen



Data
Logging



Authorized Distributor
APL ASIA CO., LTD.

11/129-132 Moo.5 Lamlukka Rd.,T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.
TEL. 0-2995-4461-3, FAX. 0-2995-4464



www.apl-asia.com

EMAIL : sales@apl-asia.com

LINE@ : @APL-ASIA

IMPROVING TRADITIONAL WORK PROCESSES MAKES EVERYTHING SIMPLE AND RELIABLE

Elitech[®]
Innovation Preceding All


	Elitech Smart Vacuum Pump	Ordinary Vacuum Pump
START		
VACUUMING	<p>Achieving unattended operation after setting target vacuum value:</p> <ul style="list-style-type: none"> • Estimate work completion time ; • Data recording(interval can be set) ; • Detect system leakage level. 	<ul style="list-style-type: none"> • Check the status for many times • Based on the change of vacuum value, judging the remaining working time by experience.
STOP	Automatic stop and warning when reaching the target vacuum value	Manually shut down when vacuum reaches target value.
MORE	<ul style="list-style-type: none"> • Export work log via APP (PDF or EXCEL) ; • The vacuum graph record the quality of vacuuming work ; • Automatic stop and restart (prevent the damaged pump by the high temperature of the motor or oil) . 	N/A



Authorized Distributor
 APL ASIA CO., LTD.
 11/129-132 Moo.5 Lamlukka Rd.,T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.
 TEL. 0-2995-4461-3, FAX. 0-2995-4464
 www.apl-asia.com
 EMAIL : sales@apl-asia.com
 LINE@ : @APL-ASIA

DIGITAL+AI : Think as you wish, Do as you expect

Elitech[®]
Innovation Preceding All



Authorized Distributor
APL ASIA CO., LTD.
11/129-132 Moo.5 Lamlukka Rd.,T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.
TEL. 0-2995-4461-3, FAX. 0-2995-4464
www.apl-asia.com
EMAIL : sales@apl-asia.com
LINE@ : @APL-ASIA

Elitech Tools App

Elitech[®]
Innovation Preceding All

- Motor and solenoid valve control
- Oil and motor temperature monitor
- Data logging and exporting
- Instant notifications, safe & efficient
- Vacuum graph display
- Read historical data



Authorized Distributor
APL ASIA CO., LTD.
11/129-132 Moo.5 Lamlukka Rd.,T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.
TEL. 0-2995-4461-3, FAX. 0-2995-4464
www.apl-asia.com
EMAIL : sales@apl-asia.com
LINE@ : @APL-ASIA



พร้อมเดือร์

พร้อมจําหนาย

พร้อมจําหนาย

SVP-7

SVP-9

SVP-12

V700

V900

V1200

	SVP-7	SVP-9	SVP-12	V700	V900	V1200
Pumping Rate	7 CFM (3 L/S)	9 CFM (4 L/S)	12 CFM (5 L/S)	7 CFM (3 L/S)	9 CFM (4 L/S)	12 CFM (5 L/S)
Stage	2 Stages	2 Stages	2 Stages	2 Stages	2 Stages	2 Stages
Limit Vacuum	15 Microns	15 Microns	15 Microns	15 Microns	15 Microns	15 Microns
Power Supply	110V/60HZ (220V customizable)	110V/60HZ (220V customizable)	110V/60HZ (220V customizable)	110V/60HZ (220V customizable)	110V/60HZ (220V customizable)	110V/60HZ (220V customizable)
Motor Power	3/4 HP (550 W)	1 HP (750 W)	1 HP (750 W)	3/4 HP (550 W)	1 HP (750 W)	1 HP (750 W)
Version	V1.0	V1.0	V1.0	V2.0	V2.0	V2.0
Pump Type	Dry Rotary Vane	Dry Rotary Vane	Dry Rotary Vane	Dry Rotary Vane	Dry Rotary Vane	Dry Rotary Vane
Transmission Distance	30ft /10m	30ft /10m	30ft /10m	30ft /10m	30ft /10m	30ft /10m
Weight	34.2 lbs / 14.5 kg	35.3 lbs / 15.3 kg	36.8 lbs / 16 kg	34.2 lbs / 14.5 kg	35.3 lbs / 15.3 kg	36.8 lbs / 16 kg



Authorized Distributor

APL ASIA CO., LTD.

11/129-132 Moo.5 Lamlukka Rd.,T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.

TEL. 0-2995-4461-3, FAX. 0-2995-4464

www.apl-asia.com

EMAIL : sales@apl-asia.com

LINE@ : @APL-ASIA